



## RD 8 V4A R125M (860 008)




Figure without obligation

Stainless steel wire according to EN 62561-2, for use in lightning protection systems or equipotential bonding.

Type	RD 8 V4A R125M
Part No.	860 008 ✓
Diameter Ø conductor	8 mm
Cross-section	50 mm <sup>2</sup>
Material	StSt (V4A)
Material No.	1.4571 / 1.4404
ASTM / AISI:	316Ti / 316L
Standard	based on EN 62561-2
Conductivity	≥ 1.25 m / Ohm mm <sup>2</sup>
Resistivity	≤ 0.8 Ohm mm <sup>2</sup> / m
Weight	395 g/m
Customs tariff number (Comb. Nomenclature EU)	72210010
GTIN	4013364018808
PU	125 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Conductor materials will be delivered in original coil weights only.

More conductor materials and components as specified in the standard series EN 62561-2 upon request.