



RD 10 V4A R20M (860 020)




Figure without obligation

Stainless steel wire according to EN 62561-2, for use in lightning protection and earth-termination systems or equipotential bonding.

Stainless steel wire (Rd 10 mm) for use in soil has to be made of StSt (V4A) with a molybdenum proportion > 2 % e.g. 1.4571, 1.4404, in accordance with EN 62561-2 and IEC/EN 62305-3.

Type	RD 10 V4A R20M
Part No.	860 020 ✓
Diameter Ø conductor	10 mm
Cross-section	78 mm ²
Material	StSt (V4A)
Material No.	1.4571 / 1.4404
ASTM / AISI:	316Ti / 316L
Standard	based on EN 62561-2
Conductivity	≥ 1.25 m / Ohm mm ²
Resistivity	≤ 0.8 Ohm mm ² / m
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	2.9 kA
Weight	617 g/m
Customs tariff number (Comb. Nomenclature EU)	72210010
GTIN	4013364092662
PU	20 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Conductor materials will be delivered in original coil weights only.

More conductor materials and components as specified in the standard series EN 62561-2 upon request.