


DG S 275 VA FM (952 087)


- Multi-purpose surge arrester consisting of a base part and a plug-in protection module
- Leakage-current-free series connection of a varistor and a spark gap in the pluggable protection module
- High reliability due to "Thermo Dynamic Control" SPD monitoring device



Figure without obligation



Basic circuit diagram DG S 275 VA FM



Dimension drawing DG S 275 VA FM

Modular single-pole surge arrester with a varistor connected in series with a spark gap in a pluggable protection module; with floating remote signalling contact.

Type	DG S 275 VA FM
Part No.	952 087
SPD according to EN 61643-11 / IEC 61643-11	type 2 / class II
Energy coordination with terminal equipment (≤ 10 m)	type 2 + type 3
Nominal voltage (a.c.) (U _N)	230 V (50 / 60 Hz)
Max. continuous operating voltage (a.c.) (U _C)	275V (50 / 60 Hz)
Max. continuous operating voltage (d.c.) (U _C)	350 V
Nominal discharge current (8/20 μs) (I _n)	10 kA
Max. discharge current (8/20 μs) (I _{max})	20 kA
Voltage protection level (U _P)	≤ 1.5 kV
Response time (t _a)	≤ 100 ns
Max. mains-side overcurrent protection	100 A gG
Short-circuit withstand capability for max. mains-side overcurrent protection (I _{SCCR})	25 kA _{rms}
Temporary overvoltage (TOV) (U _T) – Characteristic	440 V / 120 min. – withstand
Operating temperature range (T _U)	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (min.)	1.5 mm ² solid / flexible
Cross-sectional area (max.)	35 mm ² stranded / 25 mm ² flexible
For mounting on	35 mm DIN rail acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	1 module(s), DIN 43880
Type of remote signalling contact	changeover contact
Switching capacity (a.c.)	250 V / 0.5 A
Switching capacity (d.c.)	250 V / 0.1 A; 125 V / 0.2 A; 75 V / 0.5 A
Cross-sectional area for remote signalling terminals	max. 1.5 mm ² solid / flexible

Arrester use at 16.7 Hz – traction power supply systems

Type	DG S 275 VA FM
Part No.	952 087
– Test voltage AC (U _C)	275 V
– Nominal AC voltage (U _N)	230 V
– Nominal frequency AC (f _N)	16.7 Hz
Weight	116 g
Customs tariff number (Comb. Nomenclature EU)	85363030
GTIN	4013364127326
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.