



Not for use in wet weather

For indoor and outdoor installations

Fully insulated, massive switching stick head

Deep access into the installation

For use as operating rod for insulating protective

shutters in accordance with DIN VDE 0682 Teil 552

With plug-in coupling for extending the handle

SCS 72 STK 1500

Nominal voltage U_N	72.5 kV
Total length l_G	1500 mm
Insertion depth l_0	290 mm

Insulating tube	Glass-fibre reinforced polyester tube, Ø30 mm, grey
Switching pin	St, overall PVC sheathed, fixed
End fitting	Non-slip plastic cap / plug-in coupling for handle extension
Temperature range	-25° C ... +55° C

Ordering information

Type	SCS 72 STK 1500
Part No.	763 150
Packing unit	1 pc

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.