



The artificial leather bag with reinforced back panel allows for safe transport and easy storage of the single components.

Not for use in wet weather

For indoor and outdoor installations

Plug-in coupling protected against twisting and bridging

Easy transport due to detachable sticks

Kits for a variety of applications

For use as switching, earthing or operating stick

SCSS 36 STK 30	
Version	Switching stick kit, fully equipped
Nominal voltage	up to 36 kV
Max. total length	3450 mm
Packing unit	1 pcs.
Switching stick head	Glass-fibre reinforced polyester tube, Ø30 mm, grey, steel switching pin, sheathed overall in PVC
Operating head	Plastic coupling with T pin shaft, yellow; aluminium coupling with long T pin shaft
Insulating tube	Glass-fibre reinforced polyester tube, Ø30 mm or Ø43 mm, grey or yellow
Coupling	Plastic plug-in coupling protected against twisting, yellow or black
Ordering information	
Type	SCSS 36 STK 30
Part No.	766 323
Packing unit	1 pc

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.