

**Not for use in wet weather****For indoor and outdoor installations****Plug-in coupling protected against twisting and bridging****Easy transport due to self-guiding coupling****Modular system for a variety of applications****Can be used as switching stick, earthing stick or operating stick****IS 36 STK 43 1280**

Nominal voltage	up to 36 kV
Diameter	43 mm
Handle length	560 mm
Total length l_G	1280 mm
Position	X
Packaging	1 pcs.

Switching rod head	Glass fibre reinforced polyester tube, Ø30 mm, grey, St shift pin, completely plastic coated
Operating head	Coupling with plastic T pin shaft, yellow; coupling with long aluminium T pin shaft
Insulating tube	Glass fibre reinforced polyester tube, Ø30 or Ø43 mm, grey or yellow
Coupling	Plastic plug-in coupling with protection against twisting, yellow or black

Ordering information

Type	IS 36 STK 43 1280
Part No.	766 463
Packing unit	1 pc

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.