



- Not for use in wet weather**
- For indoor and outdoor installations**
- For sealing cable ends**
- For use with operating heads of type AK SD ...**
- With safety plug-in system**
- UV-resistant**

VS GOW M12	
Brand of cable sealing end	GOW
Type of cable sealing end	F6
Thread size	M12
Dimensions	M12 x 45 mm
Length	45 mm
Ordering information	
Type	VS GOW M12
Part No.	785 284
Packing unit	12 pcs

We reserve the right to modify design, technology, dimensions, weights and materials according to technical progress. Illustrations are non-binding. Pictures may differ from the modules described.