

DEHNvario

Compact 3in1 arrester for protection and availability of video transmission systems







Solution with individual components

Space-saving and applicationoptimised 3in1 arrester DEHNvario

3in1 arrester DEHNvario:

- For analogue video signals (BNC), RS485 (pan, tilt, zoom functions) and 230 V supplies
- For installation in conformity with the lightning protection zone concept at the boundaries from 0_B to 2 and higher
- High discharge capacity up to 5 kA (8/20 μs) per core
- Fast installation without tools thanks to direct plug-in technology


•	DIN r	ail n	nounted
---	-------	-------	---------

DVR BNC RS485 230	Part No. 928 440		
Interface	Power	RS485	Video
SPD class	Type 2/Class II	TYPE 2 P1	TYPE 2 P2
Nominal voltage U _N	230 V AC	5 V DC	5 V DC
Max. continuous operating voltage U _C	255 V AC	8 V DC	6,4 V DC
Nominal current IL	10 A	0.5 A	0.1 A
Cut-off frequency f_{G}	-	100 MHz	300 MHz



Technical changes, misprints and errors excepted. The pictures are not binding.





The compact 3in1 arrester protects three interfaces in a single device.

Less installation time:

The direct plug-in technology allows easy and quick conductor connection.

Reduced installation effort:

Due to the conductive DIN rail contact, the connection to the earth-termination system is ensured without additional earthing conductor.

Easy arrester exchange:

The pluggable terminal units allow fast and easy arrester replacement.

www.dehn-international.com