



RD 10 STTZN L3000 (800 910)



Figure without obligation

Steel wire according to EN 62561-2 with zinc coating $\geq 50 \mu\text{m}$ average (about 350 g/m^2), for use as air-termination or down conductor in lightning protection systems.

Type	RD 10 STTZN L3000
Part No.	800 910 ✓
Diameter \varnothing conductor	10 mm
Cross-section	78 mm^2
Material	SttZn
Standard	based on EN 62561-2
Zinc sheath	$\geq 50 \mu\text{m}$ average (about 350 g/m^2)
Conductivity	$\geq 6.66 \text{ m} / \text{Ohm mm}^2$
Resistivity	$\leq 0.25 \text{ Ohm mm}^2 / \text{m}$
Short-circuit current (50 Hz) (1 s; $\leq 300 \text{ }^\circ\text{C}$)	5.5 kA
Length	3 m
Weight	1,85 kg
Customs tariff number (Comb. Nomenclature EU)	72172030
GTIN	4013364253315
PU	10 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Conductor materials will be delivered in original coil weights only.
 More conductor materials and components as specified in the standard series EN 62561-2 upon request.