



RD 8 CU F25 HH R100M (830 038)




Figure without obligation

Copper wire according to EN 62561-2, for use in lightning protection and earth-termination systems or equipotential bonding.

Type	RD 8 CU F25 HH R100M
Part No.	830 038 ✓
Diameter Ø conductor	8 mm
Cross-section	50 mm ²
Material	Cu
Characteristics	semi-rigid F25
Standard	EN 62561-2
Conductivity	≥ 52.63 m / Ohm mm ²
Resistivity	≤ 0.019 Ohm mm ² / m
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	9.8 kA
Weight	448 g/m
Customs tariff number (Comb. Nomenclature EU)	74081100
GTIN	4013364035690
PU	100 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Conductor materials will be delivered in original coil weights only.

More conductor materials and components as specified in the standard series EN 62561-2 upon request.