



SEIL 10.5 70Q CU R50M (832 192)




Figure without obligation

Copper cable according to EN 62561-2 for use in lightning protection and earth-termination systems or equipotential bonding.

Type	SEIL 10.5 70Q CU R50M
Part No.	832 192 ✓
Cross-section	70 mm ²
Cable structure qty x Ø wire	19 x 2.1 mm
Material	Cu
Standard	EN 62561-2
Diameter Ø outside	10.5 mm
Conductivity	≥ 52.63 m / Ohm mm ²
Resistivity	≤ 0.019 Ohm mm ² / m
Short-circuit current(50 Hz) (1 s; ≤ 300 °C)	13.7 kA
Weight	597 g/m
Customs tariff number (Comb. Nomenclature EU)	74130000
GTIN	4013364018914
PU	50 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.