



SEIL 12.5 95Q CUGALSN R50M (832 295)



Figure without obligation

Copper cable, tinned, according to EN 62561-2 for use in lightning protection and earth-termination systems or equipotential bonding.

Type	SEIL 12.5 95Q CUGALSN R50M
Part No.	832 295 ✓
Cross-section	95 mm ²
Cable structure qty x Ø wire	19 x 2.5 mm
Material	Cu/gal Sn
Average of tin layer thickness	2 µm
Standard	EN 62561-2
Diameter Ø outside	12.5 mm
Conductivity	≥ 52.63 m / Ohm mm ²
Resistivity	≤ 0.019 Ohm mm ² / m
Short-circuit current(50 Hz) (1 s; ≤ 150 °C)	13.8 kA
Weight	845 g/m
Customs tariff number (Comb. Nomenclature EU)	74130000
GTIN	4013364093447
PU	50 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.