



## SEIL 9 50Q CU R50M (832 739)




Figure without obligation

Copper cable according to EN 62561-2 for use in lightning protection and earth-termination systems or equipotential bonding.

Type	SEIL 9 50Q CU R50M
Part No.	832 739 ✓
Cross-section	50 mm <sup>2</sup>
Cable structure qty x Ø wire	19 x 1.8 mm
Material	Cu
Standard	EN 62561-2
Diameter Ø outside	9 mm
Conductivity	≥ 52.63 m / Ohm mm <sup>2</sup>
Resistivity	≤ 0.019 Ohm mm <sup>2</sup> / m
Short-circuit current(50 Hz) (1 s; ≤ 300 °C)	9.8 kA
Weight	438 g/m
Customs tariff number (Comb. Nomenclature EU)	74130000
GTIN	4013364018907
PU	50 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.