

SEIL 10 V4A R100M (850 010)



Figure without obligation

Stainless steel cable for equipotential bonding.

Type	SEIL 10 V4A R100M
Part No.	850 010
Cross-section	42 mm ²
Cable structure qty x Ø wire	[7x] 19 x ca. 0.68 mm
Material	StSt (V4A)
Material No.	1.4571 / 1.4404
ASTM / AISI:	316Ti / 316L
Diameter Ø outside	10 mm
Conductivity	≥ 1.25 m / Ohm mm ²
Resistivity	≤ 0.8 Ohm mm ² / m
Tensile strength	1570 N / mm ²
Weight	395 g/m
Customs tariff number (Comb. Nomenclature EU)	73121020
GTIN	4013364129634
PU	100 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.