



RD 10 V2A R20M (860 920)




Figure without obligation

Stainless steel wire according to EN 62561-2, for use in lightning protection systems or equipotential bonding.

Type	RD 10 V2A R20M
Part No.	860 920 ✓
Diameter Ø conductor	10 mm
Cross-section	78 mm ²
Material	StSt
Material No.	1.4301 / 1.4303
Standard	based on EN 62561-2
Conductivity	≥ 1.25 m / Ohm mm ²
Resistivity	≤ 0.8 Ohm mm ² / m
Weight	617 g/m
Customs tariff number (Comb. Nomenclature EU)	72210010
GTIN	4013364092679
PU	20 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Conductor materials will be delivered in original coil weights only.

More conductor materials and components as specified in the standard series EN 62561-2 upon request.