

BA 30X3.5 TB V4A R60M (861 335)



Figure without obligation

Stainless steel strip with print every one metre, according to EN 62561-2, for use in lightning protection systems and ring equipotential bonding.

Printing:

BANDSTAHL/FLAT STRIP V4A WST 1. 4404 AISI 316L 60 M RG
DEHN-ART.NO. 861335 MAT. 3006278 DIM: 30 x 3,5 MM

Stainless steel strip for use in soil has to be made of StSt (V4A) with a molybdenum content of > 2 % e.g. 1.4571, 1.4404 in accordance with EN 62561-2 and IEC/EN 62305-3 and DIN VDE 0151.

Type	BA 30X3.5 TB V4A R60M
Part No.	861 335
Width	30 mm
Thickness	3.5 mm
Cross-section	105 mm ²
Material	StSt (V4A)
Material No.	1.4404
ASTM / AISI:	316L
Type	with print
Standard	based on EN 62561-2
Conductivity	≥ 1.25 m / Ohm mm ²
Resistivity	≤ 0.8 Ohm mm ² / m
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	3.9 kA
Weight	824 g/m
Customs tariff number (Comb. Nomenclature EU)	72202021
GTIN	4013364292628
PU	60 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.