


DG ME YPV SCI 1500 (952 520)


- Prewired modular complete unit for use in photovoltaic systems consisting of a base part and plug-in protection modules
- Combined disconnection and short-circuiting device with safe electrical isolation in the protection module (patented SCI principle)
- Tried and tested fault-resistant Y circuit



Figure without obligation



Basic circuit diagram DG ME YPV SCI 1500



Dimension drawing DG ME YPV SCI 1500

Modular multipole surge arrester with three-step d.c. switching device for PV systems.

Type	DG ME YPV SCI 1500
Part No.	952 520
SPD according to EN 50539-11	type 2
Energy coordination with terminal equipment (≤ 10 m)	type 2 + type 3
Max. PV voltage (U_{OPV})	1500 V
Short-circuit current rating (I_{SCPV})	10 kA
Total discharge current (8/20 μ s) (I_{total})	25 kA
Nominal discharge current (8/20 μ s) [(DC+/DC-) --> PE] (I_n)	12.5 kA
Voltage protection level (U_P)	≤ 6 kV
Response time (t_A)	≤ 25 ns
Operating temperature range (T_U)	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (min.)	1.5 mm ² solid / flexible
Cross-sectional area (max.)	35 mm ² stranded / 25 mm ² flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	4.5 module(s), DIN 43880
Approvals	KEMA, UL
Weight	501 g
Customs tariff number (Comb. Nomenclature EU)	85363030
GTIN	4013364149069
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.