

Accessories for HVI power Conductor / HVI power long Conductor

Accessories



V DBS RA320 PAE 27 V 600 1180 V2A (105 468)

Tripod (hinged) with variable spacer (small) for establishing the variable sealing end of the HVI power Conductor.

With UNI earthing clamp for connecting 1x Rd 8-10 mm and 1x conductor 4-50 mm².

Adjustable to the roof inclination up to max. 10°.

The three concrete bases (Part No. 102 075, weight 8.5 kg) and base plates (Part No. 102 060) must be ordered separately.



Type	V DBS RA320 PAE 27 V 600 1180 V2A
Part No.	105 468
Material of tripod	StSt
Support of tripod	22 mm
Radius	320 mm
Number of concrete bases	3 (8.5 kg each)
Space required for tripod	930 x 850 mm
Material of spacer	StSt
Conductor support Rd	27 mm
Adjustment range of spacer	600-1180 mm
Length of variable sealing end	900-1500 mm
Max. gust wind speed (3 bases, 8.5 kg each; l = 900 mm)	170 km/h
Max. gust wind speed (3 bases, 8.5 kg each; l = 1500 mm)	104 km/h
Weight	3.74 kg
Customs tariff number (Comb. Nomenclature VAE)	85389099
GTIN	4013364381582
PU	1 Stk

