

# Accessories for HVI power Conductor / HVI power long Conductor

## Accessories



### DIDH PAE 27 D16 1270 AL V2A (105 462)

Spacer for establishing the variable sealing end of the HVI power Conductor.  
 With MV clamp for connection to the equipotential bonding (Rd 16 mm / Rd 8-10 mm).  
 Concrete base (Part No. 102 010, weight 17 kg) and base plate (Part No. 102 050) must be ordered separately.



Type	DIDH PAE 27 D16 1270 AL V2A
Part No.	105 462
Material of spacer	Al
Length of spacer	1270
Conductor support Rd	27 mm
Material of conductor holder	StSt
Clamping range Rd MV clamp	8-10 / 16 mm
Material of clamp	Al
Length of variable sealing end	350-900 mm
Max. gust wind speed (1 base, 17 kg each; l = 900 mm)	100 km/h
Max. gust wind speed (2 bases, 17 kg each; l = 900 mm)	141 km/h
Weight	892 g
Customs tariff number (Comb. Nomenclature VAE)	85389099
GTIN	4013364381537
PU	1 Stk

