


DBS KB D40.50 RA590 V2A (105 290)



Figure without obligation



Hinged design for air-termination rod D40 height up to 5500 mm or DEHNiso Combi supporting tubes, for erection with concrete bases (weight 17 kg), by means of threaded rod M16 adjustable to a roof inclination up to max. 10°.

DEHNiso Combi supporting tubes length 3200 mm with air-termination rod (nine concrete blocks) or HVI Conductor installed in outside a supporting tube length 3200 mm (nine concrete bases).

Type	DBS KB D40.50 RA590 V2A
Part No.	105 290
Material of tripod	StSt
Support	Ø40 / 50 mm
Radius	590 mm
Space required for tripod	1230 x 1370 mm
Height - Number of concrete bases	4000 / 4500 mm – 3 blocks 5000 / 5500 mm – 6 blocks
Weight	8,4 kg
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364126046
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.