



BA 30X3.5 V4A R25M (860 325)



Figure without obligation

Stainless steel strip according to EN 62561-2, for use in lightning protection systems and ring equipotential bonding.

Stainless steel strip for use in soil has to be made of StSt (V4A) with a molybdenum content of > 2 % e.g. 1.4571, 1.4404 in accordance with EN 62561-2 and IEC/EN 62305-3 and DIN VDE 0151.

| Type | BA 30X3.5 V4A R25M |
|---|--------------------------------|
| Part No. | 860 325 ✓ |
| Width | 30 mm |
| Thickness | 3.5 mm |
| Cross-section | 105 mm ² |
| Material | StSt (V4A) |
| Material No. | 1.4571 / 1.4404 |
| ASTM / AISI: | 316Ti / 316L |
| Standard | EN 62561-2 |
| Conductivity | ≥ 1.25 m / Ohm mm ² |
| Resistivity | ≤ 0.8 Ohm mm ² / m |
| Short-circuit current (50 Hz) (1 s; ≤ 300 °C) | 3.9 kA |
| Weight | 825 g/m |
| Customs tariff number (Comb. Nomenclature EU) | 72202021 |
| GTIN | 4013364093157 |
| PU | 25 m |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.