

## DV MOD NPE 50 (951 050)

- RADAX Flow spark gap technology
- Easy replacement of protection modules without tools due to module locking system with module release button






Figure without obligation



Basic circuit diagram DV MOD NPE 50



Dimension drawing DV MOD NPE 50

50 kA N-PE spark-gap-based protection module

Type	DV MOD NPE 50
Part No.	951 050
Max. continuous operating voltage (a.c.) ( $U_c$ )	255 V
Lightning impulse current (10/350 $\mu$ s) ( $I_{imp}$ )	50 kA
Specific energy (W/R)	625.00 kJ/ohms
Follow current extinguishing capability [N-PE] (a.c.) ( $I_n$ )	100 A <sub>rms</sub>
Weight	171 g
Customs tariff number (Comb. Nomenclature EU)	85363030
GTIN	4013364108073
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.