



RD 8 ALMGSI HH R21M (840 108)



Figure without obligation

DEHNalu wire according to EN 62561-2, for use in lightning protection systems as air-termination, down conductor or equipotential bonding conductor.

Al and AlMgSi must not be installed directly (without distance) on, in or under plaster, mortar or concrete, and not in soil.

| Type | RD 8 ALMGSI HH R21M |
|---|---------------------------------|
| Part No. | 840 108 ✓ |
| Diameter Ø conductor | 8 mm |
| Cross-section | 50 mm ² |
| Material | AlMgSi |
| Characteristics | semi-rigid |
| Standard | EN 62561-2 |
| Conductivity | ≥ 27.77 m / Ohm mm ² |
| Resistivity | ≤ 0.036 Ohm mm ² / m |
| Weight | 135 g/m |
| Customs tariff number (Comb. Nomenclature EU) | 76052100 |
| GTIN | 4013364080423 |
| PU | 21 m |

Note: Al and AlMgSi must not be installed directly (without distance) on, in, or under plaster, mortar or concrete, and not in soil.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Conductor materials will be delivered in original coil weights only.

More conductor materials and components as specified in the standard series EN 62561-2 upon request.