


## DV MOD 255 (951 001)


- Maximum system availability due to RADAX Flow follow current limitation
- Easy replacement of protection modules without tools due to module locking system with module release button



Figure without obligation



Basic circuit diagram DV MOD 255



Dimension drawing DV MOD 255

Spark-gap-based protection module

Type	DV MOD 255
Part No.	951 001
Max. continuous operating voltage (a.c.) ( $U_c$ )	264 V
Lightning impulse current (10/350 $\mu$ s) ( $I_{imp}$ )	25 kA
Specific energy (W/R)	156.25 kJ/ohms
Follow current extinguishing capability [L-N] (a.c.) ( $I_f$ )	50 kA <sub>rms</sub>
Follow current limitation / Selectivity	no tripping of a 20 A gG fuse up to 50 kA <sub>rms</sub> (prosp.)
Weight	192 g
Customs tariff number (Comb. Nomenclature EU)	85363090
GTIN	4013364108066
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.