



Surge protection for gutter heating systems

White Paper



Contents

Structure without external
lightning protection system

Structure with external
lightning protection system

Surge protection for gutter heating systems

White Paper



Solar radiation and waste heat from buildings may melt ice or snow even under frost conditions. Such melt water then refreezes, preventing water from draining away and causing it to back up. As a result, the roof drainage is blocked and icicles may form which involves an increased risk.

An even more serious problem is a heavy snow and ice build up on the roof that may exceed the maximum load capacity of the roof.

Gutter heating systems prevent damage provided that their reliable function is ensured even under lightning and surge conditions.

Structure without external lightning protection system

If a structure has no external lightning protection system, it can be assumed that the operator considers the probability of lightning striking the structure to be low. In this case, type 2 surge arresters according to IEC 60364-1 (HD 60364-1) must be used to protect the structure from inductive coupling.

Since both the heating bands and the temperature and moisture sensor are located outside the structure, their connecting cables are exposed to inductive coupling which may cause damage to the structure. For this reason, type 2 surge arresters are installed to protect these cables directly at the entry point into the structure and the feeder cable upstream of the control unit (**Figure 1**).

Structure with external lightning protection system

The IEC 62305-1 to 4 (EN 62305-1 to 4) standard must be observed when installing lightning protection systems on structures. In such systems, the gutters and/or downpipes are typically conductively connected to the air-termination systems and are therefore at a high potential in case of a lightning strike. Both the heating band and moisture sensor cables directly contact these lightning current carrying gutters and downpipes, meaning that lightning currents are automatically injected on the cables. For this reason, type 1 lightning current arresters must be installed directly at the point where the cables enter the structure. It must be observed that the lightning current




Figure 1 Control unit protected by surge arresters in a structure without external lightning protection system

Surge protection for gutter heating systems

White Paper




Figure 2 Installation of lightning current and surge arresters if the control unit is located far from the entry point into a structure with external lightning protection system

splits both between the down conductors directly connected to the metallic gutter and the down conductors connected to the air-termination mesh. Even if the external lightning protection system only has four down conductors, lightning currents of less than 10 to 12 kA per core are to be expected in case of LPL III. A type 2 surge arrester must be provided in the feeder cable upstream of the control unit (**Figure 2**).

Buildings with an interconnected reinforced concrete or steel frame construction (IEC 62305-4 (EN 62305-4)) are an excep-

tion. If the air-termination systems ensure that the cables beyond the roof are not hit by a lightning strike, surge protective devices according to **Figure 1** can be used.

If loss of the control unit is acceptable (the control unit and/or the incoming cables must not present a risk of fire), the structure can be protected by installing combined arresters directly at the point where the cables enter the structure (**Figure 3**).

Surge protection for gutter heating systems

White Paper




Figure 3 Installation of lightning current arresters if the control unit (loss is accepted) is located near the entry point into a structure with external lightning protection


DEHNguard

DG M TT 2P 275 (952 110)


- Prewired complete unit consisting of a base part and plug-in protection modules
- High discharge capacity due to heavy-duty zinc oxide varistors / spark gaps
- High reliability due to "Thermo Dynamic Control" SPD monitoring device



Figure without obligation



Basic circuit diagram DG M TT 2P 275



Dimension drawing DG M TT 2P 275

Modular surge arrester for use in single-phase TT and TN systems ("1+1" circuit).

Type	DG M TT 2P 275
Part No.	952 110
SPD according to EN 61643-11 / IEC 61643-11	type 2 / class II
Nominal a.c. voltage (U_N)	230 V (50 / 60 Hz)
Max. continuous operating a.c. voltage [L-N] (U_C)	275 V (50 / 60 Hz)
Max. continuous operating a.c. voltage [N-PE] (U_C)	255 V (50 / 60 Hz)
Nominal discharge current (8/20 μ s) (I_n)	20 kA
Max. discharge current (8/20 μ s) (I_{max})	40 kA
Lightning impulse current (10/350 μ s) [N-PE] (I_{imp})	12 kA
Voltage protection level [L-N] (U_P)	≤ 1.5 kV
Voltage protection level [L-N] at 5 kA (U_P)	≤ 1 kV
Voltage protection level [N-PE] (U_P)	≤ 1.5 kV
Follow current extinguishing capability [N-PE] (I_n)	100 A _{rms}
Response time [L-N] (t_A)	≤ 25 ns
Response time [N-PE] (t_A)	≤ 100 ns
Max. mains-side overcurrent protection	125 A gG
Short-circuit withstand capability for max. mains-side overcurrent protection (I_{SCCR})	50 kA _{rms}
Temporary overvoltage (TOV) [L-N] (U_T) – Characteristic	335 V / 5 sec. – withstand
Temporary overvoltage (TOV) [L-N] (U_T) – Characteristic	440 V / 120 min. – safe failure
Temporary overvoltage (TOV) [N-PE] (U_T) – Characteristic	1200 V / 200 ms – withstand
Operating temperature range (T_U)	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (min.)	1.5 mm ² solid / flexible
Cross-sectional area (max.)	35 mm ² stranded / 25 mm ² flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	2 module(s), DIN 43880
Approvals	KEMA, VDE, UL, VdS
Weight	242 g
Customs tariff number	85363030
GTIN	4013364108417
PU	1 pc(s)


DEHNguard

DG M TT 275 (952 310)


- Prewired complete unit consisting of a base part and plug-in protection modules
- High discharge capacity due to heavy-duty zinc oxide varistors / spark gaps
- High reliability due to "Thermo Dynamic Control" SPD monitoring device



Figure without obligation



Basic circuit diagram DG M TT 275



Dimension drawing DG M TT 275

Modular surge arrester for use in TT and TN-S systems ("3+1" circuit).

Type	DG M TT 275
Part No.	952 310
SPD according to EN 61643-11 / IEC 61643-11	type 2 / class II
Nominal a.c. voltage (U_N)	230 / 400 V (50 / 60 Hz)
Max. continuous operating a.c. voltage [L-N] (U_C)	275 V (50 / 60 Hz)
Max. continuous operating a.c. voltage [N-PE] (U_C)	255 V (50 / 60 Hz)
Nominal discharge current (8/20 μ s) (I_n)	20 kA
Max. discharge current (8/20 μ s) (I_{max})	40 kA
Lightning impulse current (10/350 μ s) [N-PE] (I_{imp})	12 kA
Voltage protection level [L-N] (U_P)	≤ 1.5 kV
Voltage protection level [L-N] at 5 kA (U_P)	≤ 1 kV
Voltage protection level [N-PE] (U_P)	≤ 1.5 kV
Follow current extinguishing capability [N-PE] (I_n)	100 A _{rms}
Response time [L-N] (t_A)	≤ 25 ns
Response time [N-PE] (t_A)	≤ 100 ns
Max. mains-side overcurrent protection	125 A gG
Short-circuit withstand capability for max. mains-side overcurrent protection (I_{SCCR})	50 kA _{rms}
Temporary overvoltage (TOV) [L-N] (U_T) – Characteristic	335 V / 5 sec. – withstand
Temporary overvoltage (TOV) [L-N] (U_T) – Characteristic	440 V / 120 min. – safe failure
Temporary overvoltage (TOV) [N-PE] (U_T) – Characteristic	1200 V / 200 ms – withstand
Operating temperature range (T_U)	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (min.)	1.5 mm ² solid / flexible
Cross-sectional area (max.)	35 mm ² stranded / 25 mm ² flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	4 module(s), DIN 43880
Approvals	KEMA, VDE, UL, VdS
Weight	450 g
Customs tariff number	85363030
GTIN	4013364108479
PU	1 pc(s)


DEHNshield

DSH TT 2P 255 (941 110)


- Application-optimised and prewired spark-gap-based type 1 and type 2 combined lightning current and surge arrester
- Space-saving arrester for compact and simply equipped electrical installations with reduced technical requirements
- Capable of protecting terminal equipment



Figure without obligation



Basic circuit diagram DSH TT 2P 255



Dimension drawing DSH TT 2P 255

Application-optimised and prewired combined lightning current and surge arrester for single-phase TT and TN-S systems ("1+1" circuit).

Type	DSH TT 2P 255
Part No.	941 110
SPD according to EN 61643-11 / IEC 61643-11	type 1 + type 2 / class I + class II
Energy coordination with terminal equipment (≤ 5 m)	type 1 + type 2 + type 3
Nominal a.c. voltage (U_N)	230 V (50 / 60 Hz)
Max. continuous operating a.c. voltage (U_C)	255 V (50 / 60 Hz)
Lightning impulse current (10/350 μ s) [L+N-PE] (I_{total})	25 kA
Specific energy [L+N-PE] (W/R)	156.25 kJ/ohms
Lightning impulse current (10/350 μ s) [L-N]/[N-PE] (I_{imp})	12.5 / 25 kA
Specific energy [L-N]/[N-PE] (W/R)	39.06 / 156.25 kJ/ohms
Nominal discharge current (8/20 μ s) [L-N]/[N-PE] (I_n)	12.5 / 25 kA
Voltage protection level [L-N]/[N-PE] (U_p)	≤ 1.5 / ≤ 1.5 kV
Follow current extinguishing capability [L-N]/[N-PE] (I_{fi})	25 kA _{rms} / 100 A _{rms}
Follow current limitation / Selectivity	no tripping of a 32 A gL/gG fuse up to 25 kA _{rms} (prosp.)
Response time (t_A)	≤ 100 ns
Max. mains-side overcurrent protection	160 A gL/gG
Temporary overvoltage (TOV) [L-N] (U_T) – Characteristic	440 V / 120 min. – withstand
Temporary overvoltage (TOV) [N-PE] (U_T) – Characteristic	1200 V / 200 ms – withstand
Operating temperature range (T_U)	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (L, N, PE, \pm) (min.)	1.5 mm ² solid / flexible
Cross-sectional area (L, N, PE, \pm) (max.)	35 mm ² stranded / 25 mm ² flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	2 module(s), DIN 43880
Approvals	KEMA, VDE, UL
Weight	275 g
Customs tariff number	85363030
GTIN	4013364137899
PU	1 pc(s)


DEHNshield

DSH TN 255 (941 200)


- Application-optimised and prewired spark-gap-based type 1 and type 2 combined lightning current and surge arrester
- Space-saving arrester for compact and simply equipped electrical installations with reduced technical requirements
- Capable of protecting terminal equipment



Figure without obligation



Basic circuit diagram DSH TN 255



Dimension drawing DSH TN 255

Application-optimised and prewired combined lightning current and surge arrester for single-phase TN systems.

Type	DSH TN 255
Part No.	941 200
SPD according to EN 61643-11 / IEC 61643-11	type 1 + type 2 / class I + class II
Energy coordination with terminal equipment (≤ 5 m)	type 1 + type 2 + type 3
Nominal a.c. voltage (U_N)	230 V (50 / 60 Hz)
Max. continuous operating a.c. voltage (U_C)	255 V (50 / 60 Hz)
Lightning impulse current (10/350 μ s) [L+N-PE] (I_{total})	25 kA
Specific energy [L+N-PE] (W/R)	156.25 kJ/ohms
Lightning impulse current (10/350 μ s) [L, N-PE] (I_{imp})	12.5 kA
Specific energy [L,N-PE] (W/R)	39.06 kJ/ohms
Nominal discharge current (8/20 μ s) [L/N-PE]/[L+N-PE] (I_n)	12.5 / 25 kA
Voltage protection level [L-PE]/[N-PE] (U_P)	≤ 1.5 / ≤ 1.5 kV
Follow current extinguishing capability a.c. (I_{fi})	25 kA _{rms}
Follow current limitation / Selectivity	no tripping of a 32 A gL/gG fuse up to 25 kA _{rms} (prosp.)
Response time (t_A)	≤ 100 ns
Max. mains-side overcurrent protection	160 A gL/gG
Temporary overvoltage (TOV) [L-N] (U_T) – Characteristic	440 V / 120 min. – withstand
Operating temperature range (T_U)	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (L, N, PE, \pm) (min.)	1.5 mm ² solid / flexible
Cross-sectional area (L, N, PE, \pm) (max.)	35 mm ² stranded / 25 mm ² flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	2 module(s), DIN 43880
Approvals	KEMA, VDE, UL
Weight	250 g
Customs tariff number	85363030
GTIN	4013364138209
PU	1 pc(s)


BLITZDUCTOR XT

BXT ML2 BE S 5 (920 220)


- LifeCheck SPD monitoring function
- Optimal protection of two single lines and the cable shield
- For use in conformity with the lightning protection zone concept at the boundaries from $0_A - 2$ and higher



Figure without obligation



Basic circuit diagram BXT ML2 BE S 5



Dimension drawing BXT ML2 BE S 5

Space-saving combined lightning current and surge arrester module with LifeCheck feature for protecting two single lines sharing a common reference potential as well as unbalanced interfaces, with direct or indirect shield earthing. If LifeCheck detects thermal or electrical overload, the arrester has to be replaced. This status is indicated contactlessly by the DEHNrecord LC / SCM / MCM reader.

Type	BXT ML2 BE S 5
Part No.	920 220
SPD monitoring system	LifeCheck
SPD class	TYPE 1P
Nominal voltage (U_N)	5 V
Max. continuous operating d.c. voltage (U_C)	6.0 V
Max. continuous operating a.c. voltage (U_C)	4.2 V
Nominal current at 45 °C (I_L)	1.0 A
D1 Total lightning impulse current (10/350 μ s) (I_{imp})	9 kA
D1 Lightning impulse current (10/350 μ s) per line (I_{imp})	2.5 kA
C2 Total nominal discharge current (8/20 μ s) (I_n)	20 kA
C2 Nominal discharge current (8/20 μ s) per line (I_n)	10 kA
Voltage protection level line-line for I_{imp} D1 (U_p)	≤ 29 V
Voltage protection level line-PG for I_{imp} D1 (U_p)	≤ 27 V
Voltage protection level line-line at 1 kV/ μ s C3 (U_p)	≤ 18 V
Voltage protection level line-PG at 1 kV/ μ s C3 (U_p)	≤ 9 V
Series resistance per line	1.0 ohm(s)
Cut-off frequency line-PG (f_c)	1.0 MHz
Capacitance line-line (C)	≤ 2.7 nF
Capacitance line-PG (C)	≤ 5.4 nF
Operating temperature range (T_U)	-40 °C ... +80 °C
Degree of protection (plugged-in)	IP 20
Pluggable into	BXT BAS / BSP BAS 4 base part
Earthing via	BXT BAS / BSP BAS 4 base part
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21, UL 497B
SIL classification	up to SIL3 ^{*)}
ATEX approvals	DEKRA 11ATEX0089 X: II 3 G Ex nA IIC T4 Gc
IECEx approvals	DEK 11.0032X: Ex nA IIC T4 Gc
CSA & USA Hazloc approvals (1)	2516389: Class I Div. 2 GP A, B, C, D T4
CSA & USA Hazloc approvals (2)	2516389: Class I Zone 2, AEx nA IIC T4
Approvals	CSA, GOST, VdS
Weight	36 g
Customs tariff number	85363010
GTIN	4013364118331
PU	1 pc(s)

^{*)}For more detailed information, please visit www.dehn-international.com.


BLITZDUCTOR XT

BXT BAS (920 300)


- Four-pole version for universal use with all types of BSP and BXT / BXTU protection modules
- No signal interruption if the protection module is removed
- Universal design without protection elements



Figure without obligation



Basic circuit diagram with and without plugged-in module



Dimension drawing BXT BAS

The BLITZDUCTOR XT base part is a very space-saving and universal four-pole feed-through terminal for the insertion of a protection module without signal interruption if the protection module is removed. The snap-in mechanism at the supporting foot of the base part allows the protection module to be safely earthed via the DIN rail. Since no components of the protective circuit are situated in the base part, only the protection modules must be maintained.

Type Part No.	BXT BAS 920 300
Operating temperature range (T _U)	-40 °C ... +80 °C
Degree of protection	IP 20
For mounting on	35 mm DIN rails acc. to EN 60715
Connection (input / output)	screw / screw
Signal disconnection	no
Cross-sectional area, solid	0.08-4 mm ²
Cross-sectional area, flexible	0.08-2.5 mm ²
Tightening torque (terminals)	0.4 Nm
Earthing via	35 mm DIN rails acc. to EN 60715
Enclosure material	polyamide PA 6.6
Colour	yellow
ATEX approvals	DEKRA 11ATEX0089 X: II 3 G Ex nA IIC T4 Gc ^{*)}
IECEx approvals	DEK 11.0032X: Ex nA IIC T4 Gc ^{*)}
Approvals	CSA, VdS, UL, GOST
Weight	34 g
Customs tariff number	85369010
GTIN	4013364109179
PU	1 pc(s)

^{*)} only in connection with an approved protection module



**Surge Protection
Lightning Protection
Safety Equipment
DEHN protects.**

DEHN + SÖHNE
GmbH + Co.KG.

Hans-Dehn-Str. 1
Postfach 1640
92306 Neumarkt
Germany

Tel. +49 9181 906-0
Fax +49 9181 906-1100
info@dehn.de
www.dehn-international.com



www.dehn-international.com/partners

Type designations of products mentioned in the white paper being at the same time registered trademarks are not especially marked. So if there is no marking of TM or © this does not mean that the type designation is a free trade name. Neither it can be seen whether patents or utility models and other intellectual and industrial property rights are available. We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation. Misprints, errors and modifications excepted. Reproduction in any form whatsoever is forbidden without our authorisation.

actiVsense, BLITZDUCTOR, BLITZPLANER, DEHN, DEHN Logo, DEHN schützt, DEHNBloc, DEHNfix, DEHNgrip, DEHNguard, DEHNport, DEHNQUICK, DEHNrapid, DEHNshield, DEHNSnap, DEHNventil, HVI, LifeCheck, Red/Line are protected by German Trade Mark, by Community Trade Mark (EU) and/or in other countries.

Foto "Ice dam on slate roof" by Dmccroof (http://commons.wikimedia.org/wiki/File:Ice_dam_slate_roof.jpg); Licence: CC BY-SA 3.0 (<http://creativecommons.org/licenses/by-sa/3.0/>)