

## DARC STG (781 000)

- Visual detection of an arc fault by means of three sensors and activation of the short-circuiting cartridges
- Visual and acoustic indication of the activation
- Self-testing element



Figure without obligation




Figure without obligation

| Type<br>Part No.                              | DARC STG<br>781 000                |
|---|------------------------------------|
| Nominal voltage ( $U_N$ )                     | 230 V                              |
| Frequency                                     | 50 Hz                              |
| Overvoltage category                          | CAT II                             |
| Rated impulse withstand voltage               | 2.5 kV                             |
| Typical operating current consumption         | 0.25 A                             |
| Typical power consumption                     | 60 VA                              |
| Degree of protection                          | IP 20 (IP 30 in a connected state) |
| Protection class                              | 2                                  |
| Enclosure dimensions (without sensors)        | 200 x 300 x 400 mm                 |
| Enclosure dimensions with sensors             | 200 x 350 x 650 mm                 |
| Weight  | 12 kg                              |
| Customs tariff number (Comb. Nomenclature EU) | 85389099                           |
| GTIN  | 4013364151086                      |
| PU  | 1 pc(s)                            |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

For more detailed information on the arc fault protection system DEHNarc, see installation instructions No. 1749.