

## SEIL 8 V4A R100M (850 008)



Figure without obligation

Stainless steel cable for equipotential bonding.

Type	SEIL 8 V4A R100M
Part No.	850 008
Cross-section	27 mm <sup>2</sup>
Cable structure qty x Ø wire	[7x] 19 x ca. 0.59 mm
Material	StSt (V4A)
Material No.	1.4571 / 1.4404
ASTM / AISI:	316Ti / 316L
Diameter Ø outside	8 mm
Conductivity	≥ 1.25 m / Ohm mm <sup>2</sup>
Resistivity	≤ 0.8 Ohm mm <sup>2</sup> / m
Tensile strength	1570 N / mm <sup>2</sup>
Weight	235 g/m
Customs tariff number (Comb. Nomenclature EU)	73121020
GTIN	4013364129627
PU	100 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.