



SEIL 14.5 120Q CUGALSN R50M (832 320)



Figure without obligation

Copper cable, tinned, according to EN 62561-2 for use in lightning protection and earth-termination systems or equipotential bonding.

| Type | SEIL 14.5 120Q CUGALSN R50M |
|---|---------------------------------|
| Part No. | 832 320 ✓ |
| Cross-section | 120 mm ² |
| Cable structure qty x Ø wire | 19 x 2.8 mm |
| Material | Cu/gal Sn |
| Average of tin layer thickness | 2 µm |
| Standard | EN 62561-2 |
| Diameter Ø outside | 14.5 mm |
| Conductivity | ≥ 52.63 m / Ohm mm ² |
| Resistivity | ≤ 0.019 Ohm mm ² / m |
| Tensile strength | 200 N / mm ² |
| Short-circuit current(50 Hz) (1 s; ≤ 150 °C) | 17.3 kA |
| Weight | 1,06 kg/m |
| Customs tariff number (Comb. Nomenclature EU) | 74130000 |
| GTIN | 4013364129641 |
| PU | 50 m |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions and materials upon request.